

Eaton BR250ST

Catalog Number: BR250ST

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on shunt trip circuit breaker, 50 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters, Shunt trip included



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR250ST
	UPC
	786676000345
Product Length/Depth	Product Height
4.25 in	3.5 in
Product Width	Product Weight
4 in	0.94 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on shunt trip circuit breaker

Special features

Shunt trip

Amperage Rating

50 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Shunt trip

Included

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR250ST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)