

Eaton BR270

Catalog Number: BR270

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 70 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #8-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters

General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR270
	UPC
	786676363150
Product Length/Depth	Product Height
2.8 in	2.5 in
Product Width	Product Weight
1.9 in	0.65 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489



defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Special features

Used with Type BR Loadcenters

Amperage Rating

70A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#8-1/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - BR270



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)