

# Eaton BR3030B150R

Catalog Number: BR3030B150R

No feed-thru lugs, Main circuit breaker loadcenter, 150A, C3R, Aluminum, Interlock cover, NEMA 3R, Metallic, 10 kAIC, BR, 30 circuits, Thirty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BR3030B150R
<b>UPC</b>	<b>Product Length/Depth</b>
786676445108	5.19 in
<b>Product Height</b>	<b>Product Width</b>
25 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
42 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Main circuit breaker loadcenter

### Amperage Rating

150 A

### Bus material

Aluminum

### Cover

Interlock cover

### Main circuit breaker

BR

### Number of circuits

30

### Number Of Poles

30-pole

### Number of spaces

30

### Phase

Single-phase

### Wire size

#2/0 AWG-300 kcmil Cu/Al

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

C3R

### Enclosure

NEMA 3R

### Enclosure material

Metallic

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR3030B150R

Interrupt rating

10 kAIC

Number of wires

3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)