

Eaton BR3040B200RV

Catalog Number: BR3040B200RV

No feed-thru lugs, Main circuit breaker loadcenter, 200A, D1R, Aluminum, Interlock cover, NEMA 3R, Metallic, 25 kAIC, BWH, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR3040B200RV
UPC	Product Length/Depth
786676002226	5.19 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
40.62 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	Includes 5-br120 & 1 br230

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Interlock cover

Main circuit breaker

BWH

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

D1R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR3040B200RV

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia