

Specifications

Eaton BR3040B200RV

No feed-thru lugs, Main circuit breaker loadcenter, 200A, D1R, Aluminum, Interlock cover, NEMA 3R, Metallic, 25 kAIC, BWH, 40 circuits, Forty pole, 30 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V

General specifications

PRODUCT NAME	Eaton BR main breaker loadcenter
CATALOG NUMBER	BR3040B200RV
UPC	786676002226
PRODUCT LENGTH/DEPTH	5.19 in
PRODUCT HEIGHT	29.13 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	40.62 lb
WARRANTY	10 year
CERTIFICATIONS	UL 50 UL 67
CATALOG NOTES	Includes 5-br120 & 1 br230

Product specifications

SPECIAL FEATURES	No feed-thru lugs
TYPE	Main circuit breaker loadcenter
AMPERAGE RATING	200 A
BUS MATERIAL	Aluminum
COVER	Interlock cover
MAIN CIRCUIT BREAKER	BWH
NUMBER OF CIRCUITS	40
NUMBER OF SPACES	30
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil Cu/Al
MOUNTING	Combination
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240 V
BOX SIZE	D1R
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BR3040B200RV
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

