



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR3040B200V2

UPC:782114894460

Dimensions:

- **Height:** 23 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

Weight:44 LB

Notes:Includes 10-br120 &1-br230

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs, includes BREQS125 hold-down screw
- **Type:** Main circuit breaker
- **Amperage Rating:** 200A
- **Box Size:** C2
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)



- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR3040B200V2](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.