

Eaton BR3040N200RG

Catalog Number: BR3040N200RG

Eaton BR convertible loadcenter, Ground bar|value pack, Convertible main, 200 A, D1, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, Combination, 40 Circuits, 30 Spaces, Three-wire, Single-phase, 120/240 V, Determined by circuit breaker installed



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR3040N200RG
UPC	Product Length/Depth
782116893935	3.88 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
40 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Ground bar
value pack

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

40

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

D1

Enclosure

NEMA 3R

Enclosure material

Metallic

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE,
OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR3040N200RG

Interrupt rating

25 kAIC

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia