

# Eaton BR3060BQN200R

Catalog Number: BR3060BQN200R

Quick connect neutrals, Main circuit breaker loadcenter, 200A, G1R, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 60 circuits, 30 spaces, Three-wire, Single-phase, #2 AWG-300 kcmil, Combination, Type BR 1-inch breakers, 120/240V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BR3060BQN200R
<b>UPC</b>	<b>Product Length/Depth</b>
786676026253	5.19 in
<b>Product Height</b>	<b>Product Width</b>
34.13 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
39 lb	10 year
<b>Certifications</b>	
UL Listed file E52977	

## defaultTaxonomyAttributeLabel

### Special features

Quick connect neutrals

### Type

Main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

G1R

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BR3060BQN200R

Number of wires

3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)