

# Eaton BR3060NQN200

Catalog Number: BR3060NQN200

BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, I1 box size

## General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR3060NQN200
UPC	Product Length/Depth
786676026369	3.88 in
Product Height	Product Width
34.13 in	14.31 in
Product Weight	Warranty
34 lb	10 year

## Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.



defaultTaxonomyAttributeLabel	Resources
<p><b>Amperage Rating</b></p> <p>200 A</p>	<p><b>Brochures</b></p> <p><a href="#">Loadcenters and Circuit Breakers</a></p>
<p><b>Bus material</b></p> <p>Aluminum</p>	<p><b>Specifications and datasheets</b></p> <p><a href="#">Eaton Specification Sheet - BR3060NQN200</a></p>
<p><b>Cover</b></p> <p>Cover included</p>	
<p><b>Mounting</b></p> <p>Combination</p>	
<p><b>Number of circuits</b></p> <p>60</p>	
<p><b>Number of spaces</b></p> <p>30</p>	
<p><b>Phase</b></p> <p>Single-phase</p>	
<p><b>Used with</b></p> <p>Type BR 1-inch breakers</p>	
<p><b>Voltage rating</b></p> <p>120/240 V</p>	
<p><b>Wire size</b></p> <p>Determined by circuit breaker installed</p>	
<p><b>Box size</b></p> <p>G1</p>	
<p><b>Enclosure</b></p> <p>NEMA 1</p>	
<p><b>Enclosure material</b></p> <p>Metallic</p>	
<p><b>Interrupt rating</b></p> <p>10 kAIC</p>	
<p><b>Number of wires</b></p> <p>3</p>	



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)