

# Eaton BR320

Catalog Number: BR320

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, Three-pole, 240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BR320
	UPC
	786676367752
<b>Product Length/Depth</b>	<b>Product Height</b>
2.9 in	2.7 in
<b>Product Width</b>	<b>Product Weight</b>
2.9 in	0.95 lb
<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL 489

## defaultTaxonomyAttributeLabel

### Type

Type BR 1-Inch plug-on circuit breaker

### Amperage Rating

20 A

### Voltage rating

240 V - 240 V

### Trip Type

Common breaker trip

### Circuit breaker type

BR

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Three-pole

### Quantity

28

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR320](#)