

Eaton BR380

Catalog Number: BR380

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 80 A, 10 kAIC, Three-pole, 240V, BR, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BR, Type BR Loadcenters



General specifications

| | |
|-------------------------------------------------|----------------------------------------------|
| Product Name | Catalog Number |
| Eaton BR thermal magnetic circuit breaker | BR380 |
| | UPC |
| | 782114103098 |
| Product Length/Depth | Product Height |
| 2.9 in | 2.7 in |
| Product Width | Product Weight |
| 2.9 in | 1 lb |
| Warranty | Compliances |
| Limited lifetime residential, 1 year commercial | Federal Specifications Classification W-C375 |
| Certifications | |
| UL 489 | |

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

80 A

Voltage rating

240 V - 240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#4-1/0 AWG Cu/Al

Number of poles

Three-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR380](#)