

Eaton BR thermal magnetic circuit breaker

BR390

UPC:786676368056

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 3 IN

Weight:.99 LB

Warranties: No Data

Specifications:

- **Type:** Type BR 1-Inch plug-on circuit breaker
- **Amperage Rating:** 90A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Main Circuit Breaker:** BR
- **Trip Type:** Common breaker trip
- **Wire Size:** #4-1/0 AWG Cu/Al
- **Quantity:** Q28
- **Used With:** Type BR Loadcenters

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BR390](#)

Certifications:

- UL 489

Product compliance:

- Federal Specifications Classification W-C375

