



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street
75766-0000, TX Jacksonville
Phone: 903-586-2904
Fax: 903-586-5271



BR4040L200G 40/40C 200A MLO Loadcenter W/Bonded Ground Bar *Eaton Corp*

Catalog Number	BR4040L200G
Manufacturer	Eaton Corp
Description	Main Lug Load Center, 40 Spaces, 40 Circuits, 200 A, 120/240 V Ac, #1 Awg to 300 Kcmil Wire Size, Metallic Material, Aluminum Bus Material, 14.31 In Overall Length, 3.88 In Overall Width, 34.13 In Overall Height
Weight per unit	34.0 (lbs/each)
Product Category	Single Phase Main Lug Load Cen

Features

amperage rating	59120
Box Size	M104D-731
cover	Cover included
Cover Type	Cover included
dimensions	98.5520millimetreX36.3474centimetreX86.6902centimetre
main circuit breaker	BWH
number of spaces	40 W
Number of Wires	Three-wire
Phase	1 PH
used with	Type BR 1-inch breakers

Material, Color, and Finish

Enclosure Material	Metallic
--------------------	----------

Dimensions and Weight

Size	M104D-731
------	-----------

Descriptions

Description	40/40C 200A MLO LOADCENTER W/BONDED GROUND BAR
extra long description	ETN BR4040L200G BR style 1-inch loa
Special Features	Ground bar

Manufacturer Information

GTIN	00782116972609
UPC	782116972609



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street
75766-0000, TX Jacksonville
Phone: 903-586-2904
Fax: 903-586-5271

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND
Type	MAIN LUG
unspsc code	39121101

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	34

Uses, Certifications, and Standards

Enclosure	NEMA 1
Mounting	Combination
standard	UL 67;UL 50