

Eaton BR4040N200R

Catalog Number: BR4040N200R

Eaton BR convertible loadcenter, No feed-thru lugs, includes BREQS125 hold-down screw, Convertible main, 200 A, C4, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, Combination, 40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR4040N200R
UPC	Product Length/Depth
786676449052	3.88 in
Product Height	Product Width
27 in	14.31 in
Product Weight	Warranty
34 lb	10 year
Certifications	Catalog Notes
UL 50 UL 67	The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

defaultTaxonomyAttributeLabel

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

40

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

C4

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR4040N200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia