

Eaton BR4040N200RG

Catalog Number: BR4040N200RG

Eaton BR convertible loadcenter, Ground bar, includes BREQS125 hold-down screw, Convertible main, 200 A, C4, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, Combination, 40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR4040N200RG
UPC	Product Length/Depth
782116893959	3.88 in
Product Height	Product Width
27 in	14.31 in
Product Weight	Warranty
34 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Special features

Ground bar, includes BREQS125 hold-down screw

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Mounting

Combination

Number of circuits

40

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

C4

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Specifications and datasheets

[Eaton Specification Sheet - BR4040N200RG](#)

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)