

Eaton BR4050N200

Catalog Number: BR4050N200

Loadcenter, Single-phase, Convertible main, Factory integrated surge, 40 spaces, 50 circuits, Aluminum bus, Top or bottom feed, NEMA 1, 120/240V, 200A



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR4050N200
UPC	Product Length/Depth
786685931449	41 in
Product Height	Product Width
4.5 in	16 in
Product Weight	Warranty
34 lb	10 year
Compliances	Certifications
UL67	UL E52977

defaultTaxonomyAttributeLabel

Special features

Factory integrated surge

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Feed type

Top/bottom

Voltage rating

120/240 V

Enclosure

NEMA 1

Interrupt rating

25 kAIC

NEMA rating

NEMA 1

Resources

Brochures

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR4050N200