

Eaton BR4050N200R

Catalog Number: BR4050N200R

Factory integrated surge, Convertible main circuit breaker loadcenter, 200A, Aluminum, NEMA 3R, 50 circuits, 40 spaces, Top/bottom, 120/240V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BR4050N200R
UPC	Product Length/Depth
786685931456	4.9 in
Product Height	Product Width
39 in	14.3 in
Product Weight	Warranty
28 lb	10 year
Compliances	Certifications
UL67	UL Listed file E52977

defaultTaxonomyAttributeLabel

Special features

Factory integrated surge

Type

Convertible main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Number of circuits

50

Number of spaces

40

Phase

Single-phase

Feed type

Top/bottom

Voltage rating

120/240 V

Enclosure

NEMA 3R

Interrupt rating

25 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Specifications and datasheets

[Eaton Specification Sheet - BR4050N200R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)