

Eaton BR420

Catalog Number: BR420

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 20 A, 10 kAIC, Four-pole, 120/240V, BR, Independent, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters



General specifications

Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BR420

UPC

786676372152

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.5 lb

Compliances

Federal Specifications Classification W-C375

Certifications

UL 489

Catalog Notes

Non- CTL. Breaker does not have rejection tab feature.

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Special features

Used with Type BR Loadcenters

Amperage Rating

20 A

Voltage rating

120/240 V

Trip Type

Independent

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR420](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)