

Eaton BR4242B300R

Catalog Number: BR4242B300R

Main circuit breaker loadcenter,300A,47,Aluminum,NEMA 3R,Galvanized steel,42 circuits,42 spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR4242B300R
UPC	Product Length/Depth
786685956244	66.56 in
Product Height	Product Width
6.38 in	16.31 in
Product Weight	Warranty
102 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Main circuit breaker loadcenter

Amperage Rating

300 A

Bus material

Aluminum

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

47

Enclosure

NEMA 3R

Enclosure material

Galvanized steel

Interrupt rating

22 KAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BR4242B300R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia