

# Eaton BR4242B300R

Catalog Number: BR4242B300R

Main circuit breaker loadcenter,300A,47,Aluminum,NEMA 3R,Galvanized steel,42 circuits,42 spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V

## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR4242B300R
UPC	Product Length/Depth
786685956244	66.56 in
Product Height	Product Width
6.38 in	16.31 in
Product Weight	Warranty
102 lb	10 year
Certifications	
UL 67	
UL 50	



## defaultTaxonomyAttributeLabel

### Type

Main circuit breaker loadcenter

### Amperage Rating

300 A

### Bus material

Aluminum

### Number of circuits

42

### Number of spaces

42

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

47

### Enclosure

NEMA 3R

### Enclosure material

Galvanized steel

### Interrupt rating

22 KAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR4242B300R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)