



Powering Business Worldwide

pe.eaton.com

Eaton BR style 1-inch loadcenter

BR4242L225R

UPC:786676447904

Dimensions:

- **Height:** 39 IN
- **Length:** 5.2 IN
- **Width:** 14.3 IN

Weight:37.2 LB

Warranties:

- 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main lug
- **Amperage Rating:** 225A
- **Box Size:** L1r
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #1-300 kcmil Cu/Al at 60°C or 75°C

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type BR Arc Fault Circuit Breakers and](#)



Loadcenters

- Eaton Specification Sheet - BR4242L225R
- Dimensional Drawing - BR 1 LOADCENTER,
MAIN LUG ONLY, OUTDOOR NEMA 3R,
120/240 VAC, 1 PHASE

Certifications:

- UL 67
- UL 50

Product compliance: No Data