

# Eaton BR4242L225R

Catalog Number: BR4242L225R

Eaton Eaton BR main lug loadcenter, 225 A, L1R, Aluminum, NEMA 3R, Metallic, 25 kAIC, BWH, NEMA 3R, 42 Circuits, Twenty-four pole, 42 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1 AWG-300 kcmil Cu/Al



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BR4242L225R
UPC	Product Length/Depth
786676447904	5.2 in
Product Height	Product Width
39 in	14.3 in
Product Weight	Warranty
37.2 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Main lug

### Amperage Rating

225 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Number of circuits

42

### Number of spaces

42

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

L1R

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Specifications and datasheets

Eaton Specification Sheet - BR4242L225R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)