

# Eaton BR4242L400F

Catalog Number: BR4242L400F

Eaton Eaton BR main lug loadcenter, With flush or NEMA type 3R cover|Indoor, 400 A, 22, Aluminum, Flush, NEMA 1, 42 Circuits, 42 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208Y/120, 240V, (1) 250–750 kcmil or (2) #3/0–250 kcmil

## General specifications



Product Name	Catalog Number
Eaton BR main lug loadcenter	BR4242L400F
UPC	Product Length/Depth
786685895444	6.31 in
Product Height	Product Width
54 in	16.22 in
Product Weight	Warranty
54 lb	10 year limited

## Certifications

UL 50  
UL 67

## defaultTaxonomyAttributeLabel

### Type

Main lug

### Amperage Rating

400 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

MLO

### Mounting

Flush

### Number of circuits

42

### Number of spaces

42

### Phase

Single-phase

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

### NEMA rating

NEMA 1

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR4242L400F](#)