

Eaton BR48B200RF

Catalog Number: BR48B200RF

Feed-through lugs, Main circuit breaker loadcenter, 200A, 8R, Aluminum, Interlock cover, NEMA 3R, Metallic, 25 kAIC, BWH, 8 circuits, Eight pole, 4 spaces, Three-wire, Single-phase, #2/0 AWG-300 kcmil Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BR48B200RF
UPC	Product Length/Depth
786676001755	4.75 in
Product Height	Product Width
27 in	10.5 in
Product Weight	Warranty
23 lb	10 year
Certifications	Catalog Notes
UL 67	Suitable for service entrance only.
UL 50	Includes through-feed lugs for both phase and neutral conductors.

defaultTaxonomyAttributeLabel

Special features

Feed-through lugs

Type

Main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Interlock cover

Main circuit breaker

BWH

Number of circuits

8

Number Of Poles

Eight-pole

Number of spaces

4

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

8R

Enclosure

NEMA 3R

Enclosure material

Metallic

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR48B200RF

Interrupt rating

25 kAIC

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)