# Eaton BR48L125RP

## Catalog Number: BR48L125RP

Eaton Eaton BR main lug loadcenter, No feed-thru lugs, Convertible main, 125 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, NEMA 1,42 Circuits, 42 Spaces,Four-wire, Three-phase, Type BR 1-inch breakers, 120/240V



## General specifications

#### **Product Name**

Eaton BR main lug loadcenter

#### **UPC**

786676001205

#### **Product Height**

13 in

### **Product Weight**

10.1 lb

#### Certifications

UL 67

UL 50

## Catalog Number

BR48L125RP

## Product Length/Depth

3.56 in

#### **Product Width**

11 in

## Warranty

10 year



## defaultTaxonomyAttributeLabel

# Special features Current design Type Main lug Amperage Rating 125 A Bus material Aluminum Cover Cover included Main circuit breaker BR Mounting Surface Number of circuits 8 **Number Of Poles** Eight-pole Number of spaces 4 Phase Single-phase Used with Type BR 1-inch breakers Voltage rating 120/240V Wire size #14-1/0 AWG Cu/AI Box size 7R

Enclosure NEMA 1

Metallic

**Enclosure material** 

## Resources

#### **Brochures**

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

## Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR48L125RP

## Interrupt rating

10 kAIC

## Number of wires

3



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia