# Eaton BR50SPAST

# Catalog Number: BR50SPAST

Eaton BR spa panel, factory installed, 50 A, #8-2 Cu/Al 60°C or 75°C, 5R box, NEMA 3R enclosure, Ground fault self-test

### General specifications



Eaton BR spa panel

UPC

786685969923

**Product Height** 

4.3 in

**Product Weight** 

4.45 lb

Compliances

NEC 680.40-680.43

Catalog Notes

Includes factory installed breaker,

ground-fault self test

Catalog Number

**BR50SPAST** 

Product Length/Depth

10.2 in

**Product Width** 

4.9 in

Warranty

10 year

Certifications

UL Listed



## defaultTaxonomyAttributeLabel

Type

BR spa panel

**Amperage Rating** 

50A

Wire size

#8-2 AWG Cu/AI

Box size

5R

Enclosure

NEMA 3R

#### Resources

#### Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - BR50SPAST



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.









Eaton.com/socialmedia