

Eaton BR612L125FDP

Catalog Number: BR612L125FDP

Eaton Eaton BR main lug loadcenter, 125 A,7,Aluminum, NEMA 1,Metallic,10 kAIC,BR,Flush,NEMA 1,12 Circuits,Twenty-four pole,6 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#14-1 AWG Cu/Al

General specifications



Product Name	Catalog Number
Eaton BR main lug loadcenter	BR612L125FDP
UPC	Product Length/Depth
786676001311	3.56 in
Product Height	Product Width
13 in	11 in
Product Weight	Warranty
9.3 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Current design

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Flush

Number of circuits

12

Number of spaces

6

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#14-1 AWG Cu/Al

Box size

7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR612L125FDP

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia