Eaton BR612L125FP

Catalog Number: BR612L125FP

Eaton Eaton BR main lug loadcenter ,Ground bar, includes BREQS125 hold-down screw,Main lug,125 A,C2,Aluminum,Cover included,NEMA 1,Metallic,10 kAIC,Combination,NEMA 1,24 Circuits,Twenty-four pole,24 Spaces,Three-wire,Single-phase



General specifications

Product Name

Eaton BR main lug loadcenter

UPC

786676002028

Product Height

13 in

Product Weight

16 lb

Certifications

UL 50

UL 67

Catalog Number

BR612L125FP

Product Length/Depth

3.56 in

Product Width

11 in

Warranty

10 year



defaultTaxonomyAttributeLabel

Special features

Current design

Type

Main lug

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover not included

Main circuit breaker

BR

Mounting

Flush

Number of circuits

12

Number of spaces

6

Phase

Single-phase

Voltage rating

120/240V

Wire size

#14-1 AWG Cu/AI

Box size

7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR612L125FP



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia