

Eaton BR816B150RF

Catalog Number: BR816B150RF

BR style 1-inch loadcenter, main circuit breaker, feed-through lug, 150A, single-phase, 16-pole, 16 circuits, 8 spaces, 120/240V, #2/0-300 kcmil Cu/Al at 60°C or 75°C, NEMA 3R enclosure, c3r box size

General specifications



Product Name

Eaton BR main breaker loadcenter

Catalog Number

BR816B150RF

UPC

786676444552

Product Length/Depth

26.5 in

Product Height

5.5 in

Product Width

15.5 in

Product Weight

30 lb

Warranty

10 year

Certifications

UL 67

UL 50

Catalog Notes

Suitable for service entrance only



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Feed-through lug

Type

Main circuit breaker

Amperage Rating

150 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

16

Number of spaces

8

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil Cu/Al

Voltage rating

120/240 V

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR816B150RF



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)