

Eaton BR816N200RF

Catalog Number: BR816N200RF

Eaton BR convertible loadcenter, Feed-through lug, Convertible main, 200 A, C3r, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, BWH, 16 Circuits, 8 Spaces, Three-wire, Single-phase, 120/240 V, Determined by circuit breaker installed

General specifications



Product Name

Eaton BR convertible loadcenter

Catalog Number

BR816N200RF

UPC

786676448451

Product Length/Depth

5.19 in

Product Height

25 in

Product Width

14.31 in

Product Weight

40 lb

Warranty

10 year

Certifications

UL 50

UL 67

Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

defaultTaxonomyAttributeLabel

Special features

Feed-through lug

Type

Convertible main

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BWH

Number of circuits

16

Number of spaces

8

Phase

Single-phase

Voltage rating

120/240 V

Wire size

Determined by circuit breaker installed

Box size

C3R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - BR 1 LOADCENTER, CSR CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Specifications and datasheets

Eaton Specification Sheet - BR816N200RF



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)