

# Eaton BRCAF120CS

Catalog Number: BRCAF120CS

Eaton BR AFCI circuit breaker, AFCI Circuit breaker, Clamshell pack, 20 A, 10 kAIC, Single-pole, 120 V, BRC, Pigtail, #14-4 AWG Cu/Al, Q30, Type BR Loadcenters



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR AFCI circuit breaker	BRCAF120CS
<b>UPC</b>	<b>Product Length/Depth</b>
786685514376	6 in
<b>Product Height</b>	<b>Product Width</b>
1.25 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.45 lb	Limited lifetime residential, 1 year commercial
<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL 1699

## Type

AFCI Circuit breaker

## Special features

Clamshell pack

## Amperage Rating

20 A

## Voltage rating

120 V

## Used with

Type BR Loadcenters

## Interrupt rating

10 kAIC

## Main circuit breaker

BR

## Connection

Pigtail

## Wire size

#14-4 AWG Cu/Al

## Number of poles

Single-pole

## Quantity

30

## Brochures

Loadcenters and Circuit Breakers

Type BR Arc Fault Circuit Breakers and Loadcenters

## Catalogs

Eaton's Volume 1—Residential and Light Commercial

## Specifications and datasheets

Eaton Specification Sheet - BRCAF120CS

Type BR (1") Combination Arc Fault Circuit Interrupter