

Eaton BRD220240

Catalog Number: BRD220240

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch quad circuit breaker, (2) 20 A, (2) 40 A, 10 kAIC, Four-pole, 120/240V, BRD, Independent, #14-4 AWG Cu/Al, BRD, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BRD220240
	UPC
	786676007221
Product Length/Depth	Product Height
3 in	3 in
Product Width	Product Weight
2 in	0.9 lb
Warranty	Compliances
Limited lifetime residential, 1 year commercial	Federal Specifications Classification W-C375
Certifications	Catalog Notes
UL 489	Non-CTL

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch quad circuit breaker

Amperage Rating

(2) 20A, (2) 40A

Voltage rating

120/240 V

Trip Type

Independent

Circuit breaker type

BR

Used with

Type BR Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRD220240](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)