

Eaton BRD250250

Catalog Number: BRD250250

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch quad circuit breaker, (2) 50 A, (2) 50 A, 10 kAIC, Four-pole, 120/240V, BRD, Independent, #14-4 AWG Cu/Al, BRD, Type BR Loadcenters

General specifications



Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BRD250250

UPC

786676007603

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.9 lb

Warranty

Limited lifetime residential, 1 year commercial

Compliances

Federal Specifications Classification W-C375

Certifications

UL 489

Catalog Notes

Non-CTL

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch quad circuit breaker

Amperage Rating

(2) Two-pole

Voltage rating

120/240 V

Trip Type

Independent

Circuit breaker type

BR

Used with

Type BR Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRD250250](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)