

Eaton BRDC220220

Catalog Number: BRDC220220

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch quad circuit breaker, (2) 20 A, (2) 20 A, 10 kAIC, Four-pole, 120/240V, BRD, Common breaker trip, #14-4 AWG Cu/Al, BRD, Type BR Loadcenters



General specifications

| | |
|---|--|
| Product Name | Catalog Number |
| Eaton BR thermal magnetic circuit breaker | BRDC220220 |
| | UPC |
| | 786676007788 |
| Product Length/Depth | Product Height |
| 2 in | 3 in |
| Product Width | Product Weight |
| 2 in | 0.78 lb |
| Warranty | Compliances |
| Limited lifetime residential, 1 year commercial | Federal Specifications Classification W-C375 |
| Certifications | Catalog Notes |
| UL 489 | Non-CTL |

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch quad circuit breaker

Amperage Rating

(2) 20A, (2) 20A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Four-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BRDC220220](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)