

# Eaton BRH120

Catalog Number: BRH120

Eaton BR thermal magnetic circuit breaker, Type BR style 1-Inch plug-on circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240V, BRH, #14-4 AWG Cu/Al, BRH, Type BR Loadcenters



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR thermal magnetic circuit breaker	BRH120
	UPC
	786676373104
<b>Product Length/Depth</b>	<b>Product Height</b>
1 in	2.5 in
<b>Product Width</b>	<b>Product Weight</b>
2.8 in	0.35 lb
<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C376	UL 490
	<b>Catalog Notes</b>
	10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting

## defaultTaxonomyAttributeLabel

### Type

Type BR style 1-Inch plug-on circuit breaker

### Special features

Used with Type BR Loadcenters

### Amperage Rating

20 A

### Voltage rating

120/240 V

### Circuit breaker type

BR

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

22 kAIC

### Main circuit breaker

BRH

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRH120](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)