

# Eaton BRHH2100

Catalog Number: BRHH2100

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 100 A, 42 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BRH, Type BR Loadcenters

## General specifications



### Product Name

Eaton BR thermal magnetic circuit breaker

### Catalog Number

BRHH2100

### UPC

786676376952

### Product Length/Depth

2.5 in

### Product Height

3 in

### Product Width

2 in

### Product Weight

0.6 lb

### Compliances

Federal Specifications Classification W-C376

### Certifications

UL 490

### Catalog Notes

10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting

## defaultTaxonomyAttributeLabel

### Type

Type BR 1-Inch plug-on circuit breaker

### Amperage Rating

100 A

### Voltage rating

120/240 V

### Trip Type

Common breaker trip

### Circuit breaker type

BR

### Used with

Type BR Loadcenters

### Mounting Method

Plug-on

### Interrupt rating

42 kAIC

### Main circuit breaker

BRH

### Wire size

#4-1/0 AWG Cu/Al

### Number of poles

Two-pole

### Quantity

28

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Metering Equipment - Utilities Servicing Texas](#)

[Eaton Specification Sheet - BRHH2100](#)