

Eaton BRHH2110

Catalog Number: BRHH2110

Eaton BR thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 110 A, 42 kAIC, Two-pole, 120/240V, BRH, Common breaker trip, #4-1/0 AWG Cu/Al, Q28, BRH, Type BR Loadcenters

General specifications



Product Name

Eaton BR thermal magnetic circuit breaker

Catalog Number

BRHH2110

UPC

786676002950

Product Length/Depth

3 in

Product Height

3 in

Product Width

2 in

Product Weight

0.6 lb

Warranty

Limited lifetime residential, 1 year commercial

Compliances

Federal Specifications Classification W-C376

Certifications

UL 490

Catalog Notes

10-150A. single-, two- and three-pole, selected amperage available in switching duty, HACR, shunt trip and high magnetic setting

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

110 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

42 kAIC

Main circuit breaker

BRH

Wire size

#4-1/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRHH2110](#)

[Metering Equipment - Utilities Servicing Texas](#)