## Specifications



## Photo is representative





## Eaton BRHX2125

Eaton BR thermal magnetic circuit breaker,Quicklag Type BRHX circuit breaker,125 A,22kAIC,Twopole,120/240V,BRHX,Noninterchangeable,125,Plug-on,BRHX

General specifications	
PRODUCT NAME	Eaton BR thermal magnetic circuit breaker
CATALOG NUMBER	BRHX2125
UPC	786689041670
PRODUCT LENGTH/DEPTH	3.1 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.9 lb
WARRANTY	1 year
CERTIFICATIONS	Contact Manufacturer



Product specifications	
AMPERAGE RATING	125
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-interchangeable
CIRCUIT BREAKER TYPE	BR
MOUNTING METHOD	Plug-on
INTERRUPT RATING	22 kAIC
MAIN CIRCUIT BREAKER	BR
CONNECTION	Plug-on
NUMBER OF POLES	Two-pole
TRIP RATING	125
ТҮРЕ	Quicklag Type BRHX circuit breaker

Resources	
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRHX2125
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



**Eaton Corporation plc** Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.









