Eaton BRNSURGE

Catalog Number: BRNSURGE

Eaton Type BR circuit breaker surge protective device, Two Pole, Surge Protective Device



General specifications

Product Name

Eaton Type BR plug on module surge protection device

Product Length/Depth

3.6 in

Product Width

3.5 in

Certifications

cUL Certified UL 1449

Catalog Number

BRNSURGE

UPC

786689353667

Product Height

2.25 in

Product Weight

0.35 lb



default Taxonomy Attribute Label

Type

Type BR

Frequency rating

50/60 Hz

Interrupt rating

10 kAIC

Nominal Discharge Current

3 kA

Protection

L-N, L-L

Measured limiting voltage

600 V

Maximum continuous operating voltage

150 V L-N, 300 V L-L

Surge current

18 kA

Short-circuit rating

10 kA

Resources

Brochures

Product Family Guide

Eaton Surge Module Product Aid

Storm season is coming. Are you prepared?

Complete Home Protection, Publication No. FL010001EN / 3PC

Eaton Solutions, Publication No. SA00404006E / VCG1302

Complete Home Protection, Publication No. BR00414002E / VCG1502

Installation instructions

Surge Module IL

Specifications and datasheets

Eaton Specification Sheet - BRNSURGE



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia