

Eaton BRP10B100RF

Catalog Number: BRP10B100RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 100A, X1, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 20 circuits, Single pole, 10 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch bre



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP10B100RF
UPC	Product Length/Depth
786689059132	18.75 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
15 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Special features

Feed through lugs

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

20

Number Of Poles

Single-pole

Number of spaces

10

Phase

Single-phase

Accessories

Feed-through lugs

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X1

Enclosure

NEMA 3R

Enclosure material

Metallic

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP10B100RF](#)

Interrupt rating

10 kAIC

Number of wires

3

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP10B100RF

Catalog Number: BRP10B100RF

Feed through lugs, Plug-on neutral main circuit breaker loadcenter, 100A, X1, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 20 circuits, Single pole, 10 spaces, Three-wire, Single-phase, Feed-through lugs, Combination, NEMA 3R, Type BR 1-inch bre



Photo is representative

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP10B100RF
UPC	Product Length/Depth
786689059132	18.75 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
15 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Special features

Feed through lugs

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

100 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

20

Number Of Poles

Single-pole

Number of spaces

10

Phase

Single-phase

Accessories

Feed-through lugs

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X1

Enclosure

NEMA 3R

Enclosure material

Metallic

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP10B100RF](#)

Interrupt rating

10 kAIC

Number of wires

3

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia