

# Eaton BRP12B100

Catalog Number: BRP12B100

Eaton BR main breaker loadcenter, Plug-on neutral main circuit breaker loadcenter, 100 A, X1, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR2100, 24 circuits, Single pole, 12 spaces, Two hots, a neutral, and a ground, Single-phase



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP12B100
UPC	Product Length/Depth
786689052935	18.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
18.5 lb	10 year
Certifications	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

100 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR2100

### Number of circuits

24

### Number Of Poles

Single-pole

### Number of spaces

12

### Phase

Single-phase

### Wire size

#6-1/0 AWG Cu/Al

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP12B100](#)

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)