

# Eaton BRP12L125G

Catalog Number: BRP12L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X0, Aluminum, NEMA 1, Metallic, 10kAIC, BR2125, Surface, flush, 24 Circuits, Twenty-four pole, 12 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP12L125G
UPC	Product Length/Depth
786689053000	16.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
16.1 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel	Resources
Type	Brochures
MLO	Loadcenters and Circuit Breakers
Amperage Rating	Specifications and datasheets
125 A	Eaton Specification Sheet - BRP12L125G
Bus material	
Aluminum	
Cover	
Cover included	
Main circuit breaker	
BR2125	
Mounting	
Surface, flush	
Number of circuits	
24	
Number Of Poles	
Single-pole	
Number of spaces	
12	
Phase	
Single-phase	
Used with	
Type BR 1-inch breakers	
Voltage rating	
120/240V	
Wire size	
#6-2/0 AWG Cu/Al	
Box size	
X0	
Enclosure	
NEMA 1	
Enclosure material	
Metallic	
Interrupt rating	
10 kAIC	

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia

# Eaton BRP12L125G

Catalog Number: BRP12L125G

Eaton Eaton BR main lug loadcenter, Ground bar, Main lug only, 125 A, X0, Aluminum, NEMA 1, Metallic, 10kAIC, BR2125, Surface, flush, 24 Circuits, Twenty-four pole, 12 Spaces, Two hots, a neutral, and a ground, Single-phase, 120/240V



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP12L125G
UPC	Product Length/Depth
786689053000	16.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
16.1 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR2125

### Mounting

Surface, flush

### Number of circuits

24

### Number Of Poles

Single-pole

### Number of spaces

12

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Wire size

#6-2/0 AWG Cu/Al

### Box size

X0

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP12L125G](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



Eaton.com/socialmedia