



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BRP12N125R BR Pon Loadcntr 125A Convertible 12 Space N3R

Eaton Corp

Catalog Number	BRP12N125R
Manufacturer	Eaton Corp
Description	Eaton BR Convertible Loadcenter, Converible, 125 A, X4, Aluminum, Cover Included, Nema 3R, Metallic, 10 Kaic, BR, Combination, 24 Circuits, Single-Pole, 12 Spaces, Three-Wire, Single-Phase, Type BR 1-Inch Breakers, 120/240 V
Weight per unit	20.0 (lbs/each)
Product Category	Single Phase Convertible Load

Features

amperage rating	125
Cover Type	Cover included
dimensions	3.8800 IN X 14.3100 IN X 25.0000 IN
interrupt rating	10 kAIC
number of spaces	12
Phase	1
Voltage Rating	120/240
Wattage	Single-pole

Dimensions and Weight

Size	X4
------	----

Descriptions

Description	BR PON LOADCNTR 125A CONVERTIBLE 12 SPACE N3R
Long Description	Eaton BR convertible loadcenter, Converible, 125 A, X4, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 24 Circuits, Single-pole, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V
Product Type	Us Vista

Manufacturer Information

Brand	EATON
GTIN	00786689059170
Manufacturers Part Number	BRP12N125R
UPC	786689059170

Taxonomies, Classifications, and Categories

Type	Convertible loadcenter
------	------------------------

Packaging

Carton	1
Weight Per each	20



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

Mounting

Combination

standard

UL 67,UL 50