

Specifications



Photo is representative



Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP16L125R
UPC	786689059200
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications

TYPE	MLO
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	32
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X1
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 3R
NUMBER OF WIRES	3

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP16L125R
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0

General specifications

PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP16L125R
UPC	786689059200
PRODUCT LENGTH/DEPTH	3.88 in
PRODUCT HEIGHT	18.75 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	15 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications

TYPE	MLO
AMPERAGE RATING	125 A
BUS MATERIAL	Aluminum
COVER	Cover included
MAIN CIRCUIT BREAKER	BR
NUMBER OF CIRCUITS	32
NUMBER OF POLES	Single-pole
NUMBER OF SPACES	16
PHASE	Single-phase
USED WITH	Type BR 1-inch breakers
VOLTAGE RATING	120/240V
BOX SIZE	X1
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	10 kAIC
NEMA RATING	NEMA 3R
NUMBER OF WIRES	3

Resources

SPECIFICATIONS AND
DATASHEETS

[Eaton Specification Sheet -
BRP16L125R](#)

WARRANTY GUIDES

[Eaton type BR circuit
breaker limited warranty
June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
[Eaton.com](https://www.eaton.com)

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

