

# Eaton BRP16L125R

Catalog Number: BRP16L125R

Eaton Eaton BR main lug loadcenter,Main lug only,125 A,X1,Aluminum, NEMA 3R,Metallic,10 kAIC,BR,NEMA 3R,32 Circuits,Single-pole,16 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240V,#6–2/0



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP16L125R
UPC	Product Length/Depth
786689059200	3.88 in
Product Height	Product Width
18.75 in	14.31 in
Product Weight	Warranty
15 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X1

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### NEMA rating

NEMA 3R

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP16L125R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)