Eaton BRP20B100V25

Catalog Number: BRP20B100V25

Value pack,Plug-on neutral main circuit breaker loadcenter,100A,X3,Aluminum,Cover included,NEMA 1,Metallic,10 kAIC,BR,40 circuits,20 spaces,Three-wire,Single-phase,#4-1/0 AWG Cu/Al,Combination,Type BR 1-inch breakers,120/240V



General specifications

Product Name

Eaton BR main breaker loadcenter

UPC

786689058203

Product Height

3.88 in

Product Weight

22.85 lb

Certifications

UL 50

UL 67

Catalog Number

BRP20B100V25

Product Length/Depth

23 in

Product Width

14.31 in

Warranty

10 year



defaultTaxonomyAttributeLabel Special features Value pack Type Plug-on neutral main circuit breaker loadcenter Amperage Rating 100 A Bus material Aluminum Cover Cover included Main circuit breaker BR Number of circuits 40 **Number Of Poles** Single-pole Number of spaces 20 Phase Single-phase Wire size #4-1/0 AWG Cu/AI

Mounting
Combination

Used with

Voltage rating 120/240 V

Box size

Enclosure NEMA 1

Metallic

Enclosure material

Type BR 1-inch breakers

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20B100V25

Interrupt rating

10 kAIC

Number of wires

3



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia