Eaton BRP20B125

Catalog Number: BRP20B125

Eaton Plug-on neutral main circuit breaker loadcenter, X3, Aluminum, Cover included, NEMA 1, Metallic, 10kAlC, BR2125, 40 circuits, Single pole, 20 spaces, Two hots, a neutral, and a ground, Single-phase, Gray, Combination, NEMA 1, Type BR 1-inch breakers

General specifications

Product Name

Eaton BR main breaker loadcenter

UPC

786689053161

Product Height 3.88 in

Product Weight

20.5 lb

Certifications

UL 67 UL 50

Catalog Number

BRP20B125

Product Length/Depth

23 in

Product Width

14.31 in

Warranty

10 year



Product specifications

Number of spaces

20

Enclosure color

Gray

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

BR2125

Enclosure

NEMA 1

Amperage Rating

125 A

Number Of Poles

Single-pole

Mounting

Combination

Enclosure material

Metallic

Type

Plug-on neutral main circuit breaker loadcenter

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Number of circuits

40

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20B125

Voltage rating

120/240 V

Box size

Х3



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia