

Eaton BRP20B200

Catalog Number: BRP20B200

Plug-on neutral main circuit breaker
loadcenter,200A,X5,Aluminum,Cover included,NEMA
1,Metallic,22kAIC,CSR2200,40 circuits,Single pole,20 spaces,Two
hots, a neutral and a ground,Single-phase,#6-1/0 AWG
Cu/Al,25,Kilo Ampere,25kAIC,Gray,Combi



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP20B200
UPC	Product Length/Depth
786689054977	29.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
28.2 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Special features

Main circuit breaker

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Wire size

#6-1/0 AWG Cu/Al

Bus Rating

25 kA

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X5

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP20B200](#)

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

22 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

25 kAIC

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)