Eaton BRP20B200R

Catalog Number: BRP20B200R

Eaton BR main breaker loadcenter, 200A, X5, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 40 circuits, Single pole, 20 spaces, Three-wire, Single-phase

General specifications

Product Name

Eaton BR main breaker loadcenter

UPC

786689059255

Product Height

5.5 in

Product Weight

19 lb

Certifications

UL 67 UL 50

Catalog Number

BRP20B200R

Product Length/Depth

29 in

Product Width

14.31 in

Warranty

10 year



Product specifications Number of spaces 20 Interrupt rating 25 kAIC Phase Single-phase Bus material Aluminum Main circuit breaker CSR Enclosure NEMA 3R Amperage Rating 200 A **Number Of Poles** Single-pole

Mounting

Combination

Enclosure material

Metallic

Туре

Plug-on neutral main circuit breaker loadcenter

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 3R

Number of wires

3

Number of circuits

40

Voltage rating

120/240 V

Box size

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20B200R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia