# Eaton BRP20L125

## Catalog Number: BRP20L125

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X2, Aluminum, NEMA 1, Metallic, 10kAIC, BR2125, NEMA1, 40 Circuits, Twenty pole, 20 Spaces, Two hots, a neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0 AWG Cu/Al

#### General specifications

**Product Name** 

Eaton BR main lug loadcenter

**UPC** 

786689053222

Product Height

3.88 in

**Product Weight** 

19.3 lb

Certifications

UL 67 UL 50

Catalog Number

BRP20L125

Product Length/Depth

21 in

**Product Width** 

14.31 in

Warranty

10 year



### Product specifications

Number of spaces

20

Interrupt rating

10 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

BR2125

**Enclosure** 

NEMA 1

Amperage Rating

125 A

**Number Of Poles** 

Single-pole

**Enclosure material** 

Metallic

Type

MLO

Cover

Cover included

Used with

Type BR 1-inch breakers

**NEMA** rating

NEMA 1

Number of wires
Two hots, neutral and ground

Number of circuits

40

Voltage rating

120/240V

Box size

X2

#### Resources

**Brochures** 

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP20L125



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia